

Temperature data logger from 0°C to 220°C (standard calibration from 25°C to 140°C, calibrable from 0°C to 220°C, only the probe above 140°C) with different lengths external probe (probes cannot be switched) on a 5 mm base (base height is not counted for probe length), managed with Windows software and USB interface. With every S-Micro a battery kit for battery replacement

is included. Battery is user replaceable and the data logger is provided with an Accredia (NIST equivalent) traceable cetificate on 6 points.

It is the smallest logger for high temperatures available on the market. L and XL versions feature a longer life battery and their operative range is extended (can be calibrated from -40°C; standard calibration range is 25 °C ÷ +140

°C). They require an interface for PC connection: DiskInterface HS Mini (for P-Micro and S-Micro only, not for L and XL versions), DiskInterface HS and Multibay.

There are also other models of high temperature data loggers, for pressure and humidity too.

Main features

- Extremely reduced size: the smallest volume available for high temeprature loggers
- With different lengths (20, 50, 100, 150 mm and on demand) rigid probe for penetration
- · Completely food grade and waterproof
- · All software calculate lethality value (F0, PU, A0 ecc.)
- · Low battery consumption for an extended battery life
- · User replaceable battery (software shows battery status)
- · Very easy to deploy in any type of package
- · Accredia (NIST equivalent) traceable calibration certificate included
- · Available extended calibration from 0°C to 220°C (order extra calibration points; in case of wide calibration range the accuracy might be worse)
- · Heat protections available for use above 140°C

Plus

- · Extremely high accuracy and precision: with an accuracy of ± 0,1°C these devices can be employed in any application involving food, pharmaceuticals, validation, laboratory and medical field
- Fast response time thanks to the 3 mm diameter probe
- · Printed reports compliant with health regulations and ISO (data are not editable in the software)
- · NO NEED TO DRILL ANY LIDS, NO NEED TO MODIFY YOUR PRODUCT PACKAGING: PROGRAM THE DATA LOGGER, PLACE IT YOU PRODUCT AND START YOUR PROCESS!

The system

The system is made up by:

- · S-Micro temperature data logger
- · DiskInterface HS Mini or DiskInterface HS or Universal Multibay
- · SPD software or TS Manager software (compatible with the FDA 21 CFR Part 11 regulation)



Applications



Food & Beverages



Sterilisation



Pasteurisation



Medical



Pharmaceutical







Laboratories

Accessories

- SPD
- TS Manager
- · DiskInterface HS Mini
- · DiskInterface HS
- · Universal multibay
- Fixing base
- Adhesive rubber for high temperatures
- · Locking bolt
- Fastening system
- Teflon protective tube
- S-Micro heat protection 1
- S-Micro heat protection 2
- Battery kit for P-Micro, S-Micro

Technical specifications

Dimensions	14 h X 17 Ø (mm)
Probe dimensions	Probe base dimensions 5 h X 14 \emptyset (mm) - Probe 20/50/100/150 l X 3 \emptyset (mm) - Probe l on demand X 3 \emptyset (mm) (I on demand: min. 10 mm / max. 175 mm. For longer probes ask for quotation)
Weight	13 gr
Materials	Stainless steel AISI316L, PEEK
Temperature range	0 °C ÷ +140 °C
Sensor temperature range	0 °C ÷ +220 °C
Standard calibration points (temperature)	25/50/75/100/125/140°C
Extra calibration points (temperature)	Within the range 0 °C ÷ +220 °C
Extra calibration points (temperature)	Up to 220°C (using the heat protections)
Temperature resolution	0,01 °C
Temperature accuracy	± 0,1 °C (within the calibration range)
Memory (n. of acquisitions)	20.224
Acquisition step	From 1 every second up, with 1 second steps
Protection degree	IP68
Battery life	560.000 acquisitions at 1 second step continuously (calculated time @25°C. Battery life may be shorter if used in low temperatures)
Software&Mobile App	SPD, TS Manager
Accessories	DiskInterface HS Mini, DiskInterface HS, Universal Multibay